

# PULSEGUARD



# The PipeGuard LP

Have you felt your pipes today?

For best value flow stabilization, where pressure is below 40 Bar, 600 psi and elastomer synthetic rubber is compatible, and external environment is corrosive




Under license from M. Prober since 1963

**FLOW**  
Fluctuations  
Smoothing  
&  
Low frequency  
Pressure  
Pulsation  
Dampening


Save 22% with standard inventory 2 port dampers and have 300% more smoothness

Pressure pulsation travels at 1400 meters per second. and must be intercepted, to be attenuated.


"Dampers that do - flow goes through - but pressure pulses - do not."




Up to 10 Hz, a small diameter long "stiff" gas bag may respond to pressure pulsations. Flow through forces it to work for you and saves "T" pieces and 3 extra flanges. whilst providing first in first out constant temperature, and in place flushability. For higher frequency response, see the "PipeHugger" range.



HP Pig



PigLP




FOR LOW FREQUENCY FLOW FLUCTUATIONS AT LOW PRESSURE, AODD & HOSE PUMPS


PipeGuard all stainless dampeners may be purchased direct from the factory with a single connection thread or flange face, provided in place flush through is not required.

(If you want to have to buy an extra "T" piece plus 3 extra fittings / flanges, and or make extra welds)

SINGLE INTEGRAL FLANGE FACE WITH STUD BOLTS are available to order.




PigLP




PigLP

The size of the dampener decreases by - just less than the square of the number of plungers, or pistons.



**SAVINGS, that more than cover the cost of your dampers.**

Because the suction dampener removes the acceleration head losses and prevents the breakup of the supply column by intercepting suction line negative pressure pulsation, the ideal supply pipe size is halved. The big connection is only needed from dampener to pump. Similarly, on the discharge system, where pipe is smaller because the ideal velocity is higher, and with pulsation intercepted, the line size cross sectional area may be halved. Small pipes cost less, and installing them costs much less.



PigLP

**STAINLESS STEEL DAMPENERS COST LESS, AND ARE SAFER THAN PLASTIC ACCUMULATORS.**

At low pressure, the energy needed to cause flow, to go up a single hole, to come to a stop, and then reverse back out again, is substantial. This results in leaving flow fluctuations in your system.

Flow through not only gives you pulse dampening at a lower cost, but also provides in place flushability, at lower connection cost. No "T" to purchase.

Twin port dampers are 22% less expensive, standard off the shelf inventory items.

Ask you customer if he wishes to DOWNLOAD A .PDF, PRINTABLE COLORED PAGE GOTO [pulseguard.com/pulsation\\_dampening/select\\_smooth\\_percentage/flow\\_or\\_pressure/PG\\_catalog/elastomer/peg/peg-p2.pdf](http://pulseguard.com/pulsation_dampening/select_smooth_percentage/flow_or_pressure/PG_catalog/elastomer/peg/peg-p2.pdf)

Search for more on line [www.pulseguard.com/pulsation\\_dampening/pulse\\_damper\\_types/bag\\_bladder\\_tube/gas\\_in\\_bag/lp\\_all\\_ss/piglp\\_all\\_pumps.htm](http://www.pulseguard.com/pulsation_dampening/pulse_damper_types/bag_bladder_tube/gas_in_bag/lp_all_ss/piglp_all_pumps.htm)