




PLAS.

TYPE/Volume/Membrane -Mtl./Pressure/Connections/ Plastic Mtl.

PiG-Plas / TW/ ---i (i=in3)/B=bladder mm x Lgth -?/---p (p=psi)/to Pmp.- to Sys./ PVC or PP

Metric - PiG-Plas / TW/---Lt =Litres/B=bag diam mm x Lgth -?/---Br=Bar)/to Pmp.- to Sys./Shell Material

PART Nbr. & ID



FOR THE SAME PRICE AS A SPARES KIT Nitrogen Process Liquid Separator Membrane Plastic

we will supply and fit a spares kit and recertify your damper for you
 This way, you allow us to see as many of our products back as possible,
 and we learn the improvements that you need.
 It is part of our ISO 9001 continuous improvement policy.



As a manufacturer of vessels to ASME VIII Div. 1 "U" stamp, we believe in regular corrosion inspection and re hydro testing.


To return an item for service, first call to ask for a RGA / RMA (Return Goods/Mtl Authorization) Nbr.

Item 2, Gas Bag part numbers are the outside diameter mm at the sealing bead followed by the Over All Length
 B= Gas Bag Example: B98-300-? where?=the bag material. N=ButadieneAcryloNitrile, E=EthylenePropyleneTerPolymer
 V=FluoroCarbonElastomer, B=Butyl, H=ChloroSulphonated Polyethylene "Hypalon", S=Silicone Rubber, Nat=Natural Rub.
 To order spares : SK=Spares Kit Example SK-B98x300-E includes the gas Bag and the necessary seals also.

Dampers That Do - FLOW goes Through - Pressure pulses do not.



In USA Call 1-888-DAMPERS, FAX 1-888-TALK-DLR,
 in UK Freephone 08080-LO-PRICE, Faxfree 0800-174088



UK Colour Fax 44 (0)161 443 1486 US Color Fax 1-910-270-0320 HOME